

Conical countersink, 90°, HSSE, single-bladed cutter

For universal use up to 1300 N/mm²

ORION[®]

Application:

For producing 90° counterbores up to 1300 N/mm².

Execution:

- Single-edge countersink with slanted hole

Advantage:

- slanted continuous hole improves chip removal



Art. no.	11515 045
Brand	ORION
Manufacturer Part Number	11515045
Countersink angle	90 Degree
Cutting material	HSSE
Shank diameter	12 mm
Number of cutting edges	1 PCS
Tool holding device	HA parallel shank
Spot-facer diameter	28 mm
Min./max. cutting edge diameter	15-20 mm
Length	90 mm
f steel 700	0.19 mm/r
Surface	Uncoated
Gross Weight	0.100 kg
Product Group	1EH

EAN

4053625033553