

## Adjustable clamps

Depressed centre



### Version:

- Heat-treated steel
- Painted
- Single depressed centre



|   |                  |
|---|------------------|
| <b>Art. no.</b>                           | <b>26138 070</b> |
| <b>Slot width</b>                         | 22 mm            |
| <b>Length</b>                             | 160 mm           |
| <b>Suitable cheese-head screw DIN 912</b> | M20, M22         |
| <b>Slot length</b>                        | 55 mm            |
| <b>Clamping shoe height</b>               | 30 mm            |
| <b>Clamping shoe width</b>                | 60 mm            |
| <b>Height</b>                             | 27 mm            |
| <b>Width 3</b>                            | 30 mm            |
| <b>Height 2</b>                           | 24 mm            |
| <b>DIN</b>                                | 6316             |

### EAN-Code

4020772071080