

Nuts

For T-grooves




Application:

For clamping in T-grooves.

Version:

- Ref. no. 010- 130 tempered, strength class 10
- Ref. no. 220- 310 tempered, strength class 10, long form



Art. no.	26195 070
Type	standard
Nominal dimension of groove	18 mm
Slot nut width	17.7 mm
Thread dimension	M16
Length	28 mm
Height	20 mm
Slot nut height	10 mm
DIN	508

EAN-Code

4020772080068