





VERBINDUNGSBRÜCKEN

□ 0,63 mm – 2 mm, isoliert

Bestell-Nr.	Typ	Isolation Griffteil	Temperaturbereich	Metallteile/Oberfläche	Bemessungsstrom	Steckweite	
			°C		A	mm	
24.0058-*	KB0,63-2,54/1	PA	-40...80	Cu(Leg) ¹⁾	8	2,54	 <p>* Farben 22 23 24 28</p>
24.0052-*	KB1-2,54	PA	-40...80	Cu(Leg) ¹⁾	10	2,54	 <p>* Farben 22 23 24 28</p>
24.0050-*	KB1-5,08	PA	-40...80	Cu(Leg) ¹⁾	10	5,08	 <p>* Farben 22 23 24 28</p>



¹⁾ Hartkupferlegierung, vergoldet