

FEATURES

- Galvanised steel construction
- Easy to inspect for damage
- Shock absorbing
- High resistance to abrasion
- Fatigue rated at 1 – times the working load limit at 20 000 cycles

RS PRO Eye Bolt M10 x 15mm

RS Stock No.: 673-692



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These Eye Bolts from our own RS PRO brand are intended for linear pulling loads in the direction of the thread.

General Specifications

Type	Eye Bolt
Working Load Limit	0.25t
Material	Carbon Steel

Mechanical Specifications

Diameter	15mm
Thread Size	M10
Thread Length	18mm
Collar Diameter	22mm
Collar Thickness	7mm
Eye Outside Diameter	33mm
Overall Height	54mm
Applications	Tensioning wires, Securing loads

