

# tasker®



## The excellence for Made in Italy



# Audio

## Cavo microfonico T32, 2x0,22 mm<sup>2</sup> FLUO extra flex in versione "pocket":

# 10 20 mt

FLUO Microphone cable T32, 2x0.22 mm<sup>2</sup> extra flex in "pocket" version:  
Cable de micrófono FLUO T32, 2x0.22 mm<sup>2</sup> extra flex en versión "pocket":  
FLUO T32 Mikrofonkabel, 2x0,22 mm<sup>2</sup> Extra Flex in der "Pocket" -Version:  
Câble de microphone FLUO T32, 2x0.22 mm<sup>2</sup>, extra flexible, version "Pocket":  
Микрофонный кабель FLUO T32, 2x0,22 мм<sup>2</sup>, очень гибкий в «карманной» версии:



# tasker®






# tasker®


...a project further...

NEW

Premium Series

## Premium Series

Code	Section	Lenght (m)	Description
<b>TK123PSF</b> <b>TK126PSF</b> <b>TK129PSF</b> <b>TK1212PSF</b>	1x0,50mm <sup>2</sup>	3 <b>SPM6.3GB-N</b> max. $\varnothing$ 6,5 mm. 6 9 12	  <p><b>Colors:</b></p> <ul style="list-style-type: none"> <li>Fluo Blue</li> <li>Fluo Green</li> <li>Fluo Yellow</li> <li>Fluo Orange</li> <li>Trasparent Bronze</li> </ul> <p><b>Code:</b></p> <ul style="list-style-type: none"> <li>B</li> <li>V</li> <li>G</li> <li>A</li> <li>TB</li> </ul> <p>Cablato audio con jack mono 6.3 maschio placcato oro (SPM6.3GB-N) da ambo i lati. Cavo unipolare extra flessibile schermato a spirale + carbon screen con sezione 1x0,50 mm<sup>2</sup>, disponibile nelle metrature da 3,6, 9 o 12 metri.</p> <p>Both side gold plated jack mono 6.3 male (SPM6.3GB-N) premade audio cable. Extra flex unipolar cable 1x0,50 mm<sup>2</sup> with spiral + carbon screen shielding available in sizes of 3,6, 9 or 12 meters.</p>
<b>TK113PSF</b> <b>TK116PSF</b> <b>TK119PSF</b> <b>TK1112PSF</b>	1x0,50mm <sup>2</sup>	3 <b>SPM90 6.3M</b> max. $\varnothing$ 6,3 mm. 6 9 12	  <p><b>Colors:</b></p> <ul style="list-style-type: none"> <li>Fluo Blue</li> <li>Fluo Green</li> <li>Fluo Yellow</li> <li>Fluo Orange</li> <li>Trasparent Bronze</li> </ul> <p><b>Code:</b></p> <ul style="list-style-type: none"> <li>B</li> <li>V</li> <li>G</li> <li>A</li> <li>TB</li> </ul> <p>Cablato audio con jack mono 6.3 maschio a 90° (SPM906.3M) da ambo i lati. Cavo unipolare extra flessibile schermato a spirale + carbon screen con sezione 1x0,50 mm<sup>2</sup>, disponibile nelle metrature da 3,6, 9 o 12 metri.</p> <p>Both side 90° jack mono male 6.3 (SPM906.3M) premade audio cable. Extra flex unipolar cable 1x0,50 mm<sup>2</sup> with spiral + carbon screen shielding available in sizes of 3,6, 9 or 12 meters.</p>
<b>TK501PSF</b>	1x0,50mm <sup>2</sup>	1 <b>SP50GRCAM-N</b> max. $\varnothing$ 6 mm. 	<p><b>Colors:</b></p> <ul style="list-style-type: none"> <li>Fluo Blue</li> <li>Fluo Green</li> <li>Fluo Yellow</li> <li>Fluo Orange</li> <li>Trasparent Bronze</li> </ul> <p><b>Code:</b></p> <ul style="list-style-type: none"> <li>B</li> <li>V</li> <li>G</li> <li>A</li> <li>TB</li> </ul> <p>Cablato audio con RCA maschio placcato oro (SP50GRCAM-N) da ambo i lati. Cavo unipolare extra flessibile schermato a spirale + carbon screen con sezione 1x0,50 mm<sup>2</sup>, lunghezza 1 metro.</p> <p>Both side gold plated male RCA (SP50GRCAM-N) premade audio cable. Extra flex unipolar cable 1x0,50 mm<sup>2</sup> with spiral + carbon screen shielding, 1 meter length.</p>
<b>TK511PSF</b>	1x0,50mm <sup>2</sup>	1 <b>SP50GRCAM-N</b> max. $\varnothing$ 6 mm. <b>SP49GRCAF-N</b> max. $\varnothing$ 6 mm.  	<p><b>Colors:</b></p> <ul style="list-style-type: none"> <li>Fluo Blue</li> <li>Fluo Green</li> <li>Fluo Yellow</li> <li>Fluo Orange</li> <li>Trasparent Bronze</li> </ul> <p><b>Code:</b></p> <ul style="list-style-type: none"> <li>B</li> <li>V</li> <li>G</li> <li>A</li> <li>TB</li> </ul> <p>Cablato audio RCA maschio placcato oro (SP50GRCAM-N) e RCA femmina placcato oro (SP49GRCAF-N). Cavo unipolare extra flessibile schermato a spirale + carbon screen con sezione 1x0,50 mm<sup>2</sup>, lunghezza 1 metro.</p> <p>Gold plated male RCA (SP50GRCAM-N) to Gold plated female RCA (SP49GRCAF-N) premade audio cable. Extra flex unipolar cable 1x0,50 mm<sup>2</sup> with spiral + carbon screen shielding, 1 meter length.</p>









# tasker®

...a project further...

NEW

## Premium Series

### Premium Series

Code	Section	Length (m)	Description
TK521PSF	1x0,50mm <sup>2</sup>	1	<p><b>SP49GRCAF-N</b> max. ø 6 mm.</p>  <p><b>GOLD</b></p> <p><b>Colors:</b>            ● Fluo Blue            ● Fluo Green            ● Fluo Yellow            ● Fluo Orange            ● Trasparent Bronze</p> <p><b>Code:</b>  B            V            G            A            TB</p> <p>Cablato audio con RCA femmina placcato oro (SP49GRCAF-N) da ambo i lati. Cavo unipolare extra flessibile schermato a spirale + carbon screen con sezione 1x0,50 mm<sup>2</sup>, lunghezza 1 metro.</p> <p> Both side gold plated female RCA (SP49GRCAF-N) premade audio cable. Extra flex unipolar cable 1x0,50 mm<sup>2</sup> with spiral + carbon screen shielding, 1 meter length.</p>
TK223PSF TK226PSF TK229PSF TK2212PSF	2x0,22mm <sup>2</sup>	3 6 9 12	<p><b>SPM6.3GB-N</b> max. ø 6,5 mm.</p>  <p><b>GOLD</b></p> <p><b>Colors:</b>            ● Fluo Blue            ● Fluo Green            ● Fluo Yellow            ● Fluo Orange            ● Trasparent Bronze</p> <p><b>Code:</b> B            V            G            A            TB</p> <p>Cablato audio con jack mono 6.3 maschio placcato oro (SPM6.3GB-N) e XLR 3 poli femmina placcato oro (SPFG3XLR-N). Cavo bilanciato extra flessibile 2x0,22 mm<sup>2</sup> schermato nelle metrature da 3, 6, 9, 12 metri.</p> <p>Gold plated jack mono male 6.3 (SPM6.3GB-N) to gold plated 3 pin female XLR (SPFG3XLR-N) premade audio cable. Extra flex shielded balanced cable 2x0,22 mm<sup>2</sup> available in sizes of 3, 6, 9, 12 meters.</p>
TK333PSF TK336PSF TK339PSF TK3312PSF	2x0,22mm <sup>2</sup>	3 6 9 12	<p><b>SPMG3XLR-N</b> max. ø 7 mm.</p>  <p><b>GOLD</b></p> <p><b>Colors:</b>            ● Fluo Blue            ● Fluo Green            ● Fluo Yellow            ● Fluo Orange            ● Trasparent Bronze</p> <p><b>Code:</b> B            V            G            A            TB</p> <p>Cablato con XLR 3 poli femmina placcato oro (SPFG3XLR-N) e XLR 3 poli maschio placcato oro (SPMG3XLR). Cavo bilanciato extra flessibile 2x0,22 mm<sup>2</sup> schermato nelle metrature da 3, 6, 9, 12 metri.</p> <p>Gold plated 3 pin female XLR (SPFG3XLR-N) to gold plated 3 pin male XLR (SPMG3XLR) premade audio cable. Extra flex shielded balanced cable 2x0,22 mm<sup>2</sup> available in sizes of 3, 6, 9, 12 meters.</p>
TK172PSF TK173PSF	2x0,22mm <sup>2</sup>	2 3	<p><b>SP82GB3,5S-N</b> max. ø 6,5 mm.</p>  <p><b>GOLD</b></p> <p><b>Colors:</b>            ● Fluo Blue            ● Fluo Green            ● Fluo Yellow            ● Fluo Orange            ● Trasparent Bronze</p> <p><b>Code:</b> B            V            G            A            TB</p> <p>Cablato audio con jack 3.5 stereo placcato oro (SP82GB3,5S-N) da ambo i lati. Cavo bilanciato extra flessibile 2x0,22 mm<sup>2</sup> schermato nelle metrature da 2 e 3 metri.</p> <p>Both side gold plated jack 3.5 stereo (SP82GB3,5S-N) premade audio cable. Extra flex shielded balanced cable 2x0,22 mm<sup>2</sup> available in sizes of 2 or 3 meters.</p>

