


Crimp Fittings

Press-armaturen

Embouts sertis

Raccordi a graffare

Racores para presión



BT

BSP Male Tapered BSPT
 Außengewindeanschluss/BSPT (Stutzen)
 Mâle BSP conique
 Maschio BSPT (maschio gas conico)
 Macho fijo BSPT

Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting			mm			mm	mm	mm	mm			mm
1G2BT4	1S2BT4	1A2BT4	R 1/8-28				-4	46,4	23,0		4,2	14		
1G4BT4	1S4BT4	1A4BT4	R 1/4-19				-4	50,6	27,2		4,2	14		
1G6BT5	1S6BT5	1A6BT5	R 3/8-19				-5	52,7	28,8		5,3	19		
1G6BT6	1S6BT6	1A6BT6	R 3/8-19				-6	54,9	29,6		6,7	19		
1G8BT6	1S8BT6	1A8BT6	R 1/2-14				-6	62,6	37,3		6,7	22		
1G6BT8	1S6BT8	1A6BT8	R 3/8-19				-8	60,6	30,9		9,6	22		
1G8BT8	1S8BT8	1A8BT8	R 1/2-14				-8	66,2	36,5		9,6	22		
1G8BT10	1S8BT10	1A8BT10	R 1/2-14				-10	67,6	38,2		12,8	24		
1G12BT10	1S12BT10	1A12BT10	R 3/4-14				-10	70,2	40,8		12,8	27		
1G8BT12	1S8BT12	1A8BT12	R 1/2-14				-12	69,2	39,0		15,5	30		
1G12BT12	1S12BT12	1A12BT12	R 3/4-14				-12	71,1	40,9		15,5	30		
1G16BT12	1S16BT12	1A16BT12	R 1-11				-12	77,0	46,8		15,5	36		
1G12BT16	1S12BT16	1A12BT16	R 3/4-14				-16	76,4	42,0		20,7	36		
1G16BT16	1S16BT16	1A16BT16	R 1-11				-16	81,2	46,8		20,7	36		
1G20BT16	1S20BT16	1A20BT16	R 1 1/4-11				-16	85,4	51,0		20,7	46		
1G16BT20	1S16BT20	1AP16BT20*	R 1-11				-20	95,6	51,6		26,6	46		
		1AT16BT20*	R 1-11				-20	95,6	51,6		26,6	46		
1G20BT20	1S20BT20	1AP20BT20*	R 1 1/4-11				-20	96,2	52,2		26,6	46		
		1AT20BT20**	R 1 1/4-11				-20	96,2	52,2		26,6	46		
1G24BT20	1S24BT20	1AP24BT20*	R 1 1/2-11				-20	98,0	54,0		26,6	50		
		1AT24BT20**	R 1 1/2-11				-20	98,0	54,0		26,6	50		
1G24BT24	1S24BT24	1A24BT24	R 1 1/2-11				-24	100,8	54,5		32,0	50		
1G32BT24	1S32BT24	1A32BT24	R 2-11				-24	106,5	60,2		32,0	65		
1G32BT32	1S32BT32	1A32BT32	R 2-11				-32	110,4	60,2		44,4	65		

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

Specification subject to change without notice