


33782/33V82 – SAE (JIC) 37° Dichtkonus mit Überwurfmutter

45° Bogen – ISO 12151-5-SWE45 – DKJ 45°

WERKSTOFF Stahl, verzinkt, transparent Cr(VI)-frei passiviert.
B: Messing; SM: metrische Schlüsselweite




Artikelnummer #	DN	size	mm	Zoll	Gewindegröße UNF	A mm	B mm	E mm	W Zoll	Max. WP MPa
33782-4-4	6	-4	6,3	1/4	7/16x20	39	20	8	9/16	1,6
33V82-4-4B-SM	6	-4	6,3	1/4	7/16x20	44	25	10	17 mm	1,6
33782-6-6	10	-6	9,5	3/8	9/16x18	53	30	10	11/16	1,6
33782-6-6-SM	10	-6	9,5	3/8	9/16x18	51	28	11	19 mm	1,6
33782-8-8	12	-8	12,7	1/2	3/4x16	54	35	14	7/8	1,6

33982/33W82 – SAE (JIC) 37° Dichtkonus mit Überwurfmutter

90° Bogen – ISO 12151-5-SWES – DKJ 90°

WERKSTOFF Stahl, verzinkt, transparent Cr(VI)-frei passiviert.
C: Edelstahl; SM: metrische Schlüsselweite



Artikelnummer #	DN	size	mm	Zoll	Gewindegröße UNF	A mm	B mm	E mm	W Zoll	Max. WP MPa
33982-4-4	6	-4	6,3	1/4	7/16x20	39	20	17	5/8	1,6
33W82-4-4C-SM	6	-4	6,3	1/4	7/16x20	39	20	21	17 mm	1,6
33982-6-6	10	-6	9,5	3/8	9/16x18	50	28	22	11/16	1,6
33982-6-6-SM	10	-6	9,5	3/8	9/16x18	47	25	23	19 mm	1,6
33982-6-6C-SM	10	-6	9,5	3/8	9/16x18	47	25	23	19 mm	1,6
33982-8-8	12	-8	12,7	1/2	3/4x16	59	33	28	7/8	1,6
33W82-8-8-SM	12	-8	12,7	1/2	3/4x16	55	29	28	22 mm	1,6
33982-10-10	16	-10	15,9	5/8	7/8x14	74	37	31	1	1,6
33982-12-12	20	-12	19,1	3/4	1-1/16x12	84	46	46	1-1/4	1,6
33982-12-12-SM	20	-12	19,1	3/4	1-1/16x12	83	46	48	32 mm	1,6