


### Modular Einbaubuchsen, 180°, 8-polig (RJ45), Top entry, geschirmt Modular Jacks, 180°, top entry, 8-poles (RJ45), shielded



**Gehäuse**  
 Polyester, glasfaserverstärkt,  
 UL94V-0, Schwarz

**Housing**  
 Polyester, glass filled,  
 UL94V-0, Black

**Kontakte**  
 Phosphorbronze

**Contacts**  
 Phosphor bronze

**Kontaktfläche**  
 6µ" Gold


**Contact finish**  
 6µ" gold

**Betriebstemperaturbereich**  
 -40°C bis +85°C

**Operating temperature**  
 -40°C to +85°C

**Strombelastbarkeit**  
 1.5A

**Current rating**  
 1.5A



Bestellcode : **A - 2014 - 2 - LP/FS**  
 Ordercode :

D-Sub / Hoods  
Centronics

Multiflex

Modular

USB

Switches

Powercords  
Powersockets

MiniDIN

DIN4161x  
Hardmetric

Sockets + Strips  
Jumper