

## MOSA M8 MALE 0° FIELD-WIREABLE (IDC)

3-pol., 0,14-0,34mm<sup>2</sup>

Male straight



3-pole


Insulation displacement technology

Connection cross section: 0.14...0.34 mm<sup>2</sup>

### [Link to Product](#)

#### Illustration





Product may differ from Image

### Approvals



### Form

08331

### Technical Data

Operating voltage	max. 32 V AC/DC
Operating current per contact	max. 4 A
Connection cross section	0.14...0.34 mm <sup>2</sup> (conductor diameter min. 0.1 mm)
Sealing range (cable diameter)	2.5...5.1 mm (gasket included)
Wire isolation	PVC, PP, TPE
Outer wire diameter	1.0...1.6 mm
Protection	IP67 inserted and tightened (EN 60529)

### General data

Temperature range	-25...+85 °C
-------------------	--------------

### Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1

