

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1716920212](#)
Status: **Active**
Overview: Mega-Fit Power Connectors
Description: Mega-Fit TPA-Capable Receptacle Housing, Dual Row, 12 Circuit, UL 94V-0, Glow-Wire Capable, Black

Documents:

Drawing (PDF)	Datasheet (PDF)
Product Specification 1054171000-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification 1716920200-000 (PDF)	

General

Product Family	Crimp Housings
Series	171692
Application	Power, Wire-to-Board, Wire-to-Wire
Datasheet Order No	987650-5401
Overview	Mega-Fit Power Connectors
Product Name	Mega-Fit
UPC	191130071142


Physical

Circuits (maximum)	12
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	6.480/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.70mm
Pitch - Termination Interface	5.70mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C, -40° to +120°C

Material Info

Reference - Drawing Numbers

Packaging Specification	1716920200-000
Product Specification	1054171000-PS-000
Sales Drawing	1716920200-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[171692](#) Series

Mates With

Mega-Fit Headers [76825](#) , [76829](#) , [172065](#) ,
[172064](#)
Mega-Fit Plug Housing [105411](#)

Use With

Mega-Fit TPA [105415](#)
Mega-Fit Crimp
Terminals [76823](#) , [172063](#) (TPA-Capable
Terminals Only)