

# Han 1A-12-c-f latch



Part number	09 10 012 3101
Specification	Han 1A-12-c-f latch
HARTING eCatalogue	https://b2b.harting.com/09100123101

Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Inserts
Series	Han <sup>®</sup> 1A

#### Version

Termination method	Crimp termination
Gender	Female
Locking type	Snap-in latches
Size	1 A
Number of contacts	12
Details	Please order crimp contacts separately.
	Order separately the single wire seal or the hoods/housings for an IP65 performance.
Details	A Han <sup>®</sup> 1A configuration that only consists of inserts (with or without strain relief, 09 10 000 5300) is an unenclosed connector. In this case protection against electric shock must be provided by the installation methods of the user.

## Technical characteristics

Conductor cross-section	0.09 0.52 mm²
Rated current	6.5 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Insulation resistance	>10 <sup>8</sup> Ω
Limiting temperature	-30 +90 °C



### Technical characteristics

Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP20

## Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	RAL 9005 (jet black)
Material (seal)	NBR
Colour (seal)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Specifications	EN 45545-2 R22: HL1, HL2, HL3 EN 45545-2 R23: HL1, HL2, HL3 EN 45545-2 R24: HL1, HL2, HL3 IEC 61373 Category 1 Class B
	EN 60664-1 IEC 61984
Approvals	DNV GL

### Commercial data

Packaging size	1
Net weight	8.72 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440205 Contact insert for industrial connectors