

## Bassi Black E27 PIR Sensor

Article code: 623173  
 EAN: 7021986231731



### Electrical

Wattage: Max 15W LED  
 Voltage: 220-240V

### Light technic

Socket: E27  
 Light distribution: Direct  
 Optic: Plastic Opal  
 Beam angle: 120°  
 Visible flicker (PstLM): 0.12  
 Stroboscopic flicker (SVM): 0.26

### Control/Dimming

Type: PIR Sensor

### Protection

Luminaire class: Class I  
 Fire protection class: 850°C - 30s

### Energy and approvals

Breem: Fulfils Hea 01 for flicker free lighting

### Materials and finish

Housing: Aluminium  
 Colour: Black (RAL 9004)  
 Optics: UV-stabilized polycarbonate

### Mounting/Connection



Mounting: Surface, Indoor / Outdoor  
 Connection: Screwless terminal block

### Dimensions


Length (mm) L: 240  
 Width (mm) W: 240  
 Height (mm) H: 110  
 Weight (kg) gross/net: 1.895 / 1.636

### Packaging

Packing dimensions (mm): 250 x 250 x 125



Sensor functions	
	Distance/range adjusting, 2-6m
	Light time adjusting, 5sec-5min
TEST	Lamp always on



7 0 2 1 9 8 6 2 3 1 7 3 1