

## Crimp Fittings

## Press-armaturen


## Embouts sertis

## Raccordi a graffare

## Racores para presión

### DL


DKO Female Swivel, Light Duty  
Dichtkopf DKOL, leichte Baureihe  
DKO série L  
Femmina girevole DKOL, serie leggera  
Hembra loca DKOL, serie ligera



Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting						mm	mm	mm	mm			mm
1G5DL3	1S5DL3	1A5DL3	M12X1,5		6	5	-3	39,7	22,2		2,5	14		
1G5DL4	1S5DL4	1A5DL4	M12X1,5		6	6	-4	44,8	21,4		4,2	14		
1G6DL4	1S6DL4	1A6DL4	M14X1,5		8	6	-4	46,0	22,6		4,2	17		
1G6DL5	1S6DL5	1A6DL5	M14X1,5		8	6	-5	46,2	22,3		5,3	17		
1G8DL4	1S8DL4	1A8DL4	M16X1,5		10	6	-4	48,2	24,8		4,2	19		
1G8DL5	1S8DL5	1A8DL5	M16X1,5		10	8	-5	50,7	26,8		5,3	19		
1G8DL6	1S8DL6	1A8DL6	M16X1,5		10	10	-6	50,5	25,2		6,7	19		
1G10DL6	1S10DL6	1A10DL6	M18X1,5		12	10	-6	51,2	25,9		6,7	22		
1G12DL8	1S12DL8	1A12DL8	M22X1,5		15	12	-8	58,3	28,6		9,6	27		
1G16DL10	1S16DL10	1A16DL10	M26X1,5		18	16	-10	59,2	29,8		12,8	32		
1G20DL12	1S20DL12	1A20DL12	M30X2,0		22	19	-12	62,5	32,3		15,5	36		
1G25DL16	1S25DL16	1A25DL16	M36X2,0		28	25	-16	68,2	33,8		20,7	41		
1G32DL20	1S32DL20	1AP32DL20*	M45X2,0		35	31	-20	83,7	39,7		26,6	50		
		1AT32DL20**	M45X2,0		35	31	-20	83,7	39,7		26,6	50		
1G40DL24	1S40DL24	1A40DL24	M52X2,0		42	38	-24	87,2	40,9		32,0	60		

### DLA

DKO Female Swivel, Light Duty, 45° Elbow  
Dichtkopf DKOL, leichte Baureihe, 45° Krümmer  
DKO série L coudé 45°  
Femmina girevole DKOL a 45°, serie leggera  
Hembra loca DKOL acodado a 45°, serie ligera



Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting						mm	mm	mm	mm			mm
1G5DLA3	1S5DLA3	1A5DLA3	M12x1,5		6	5	-3	52,7	35,2	15,2	2,5	14		
1G6DLA4	1S6DLA4	1A6DLA4	M14x1,5		8	6	-4	62,4	39,0	17,5	4,2	17		
1G8DLA5	1S8DLA5	1A8DLA5	M16x1,5		10	8	-5	64,9	41,0	18,5	5,3	19		
1G8DLA6	1S8DLA6	1A8DLA6	M16x1,5		10	10	-6	66,8	41,0	19,0	6,7	19		
1G10DLA6	1S10DLA6	1A10DLA6	M18x1,5		12	10	-6	70,0	44,7	17,6	6,7	22		
1G12DLA8	1S12DLA8	1A12DLA8	M22x1,5		15	12	-8	81,7	52,0	21,5	9,6	27		
1G16DLA10	1S16DLA10	1A16DLA10	M26x1,5		18	16	-10	91,3	61,9	22,0	12,8	32		
1G20DLA12	1S20DLA12	1A20DLA12	M30x2,0		22	20	-12	100,8	70,6	24,3	15,5	36		
1G25DLA16	1S25DLA16	1A25DLA16	M36x2,0		28	25	-16	103,1	68,7	26,6	20,7	41		
1G32DLA20	1S32DLA20	1AP32DLA20*	M45x2,0		35	32	-20	148,0	104,0	43,0	26,6	50		
		1AT32DLA20**	M45x2,0		35	32	-20	148,0	104,0	43,0	26,6	50		
1G40DLA24	1S40DLA24	1A40DLA24	M52x2,0		42	40	-24	180,5	134,2	52,2	32,0	60		

\* 1-wire  
\*\* 2-wire

\* 1-wire  
\*\* 2-wire

\* 1-wire  
\*\* 2-wire

\* 1-wire  
\*\* 2-wire

\* 1-wire  
\*\* 2-wire

Specification subject to change without notice