

PRODUCT-DETAILS

# PSBF0410

## LOW ACID PVC CVRD CONDUIT 20MM 10M



Product image  
not available

### General Information

Extended Product Type	PSBF0410
Product ID	7TCA297020R0307
EAN	5011949214439
Catalog Description	LOW ACID PVC CVRD CONDUIT 20MM 10M
Long Description	Liquid Tight, Pliable Conduit, Nominal Conduit Size 20mm, 1/2 Inch US Trade Size, Outside Diameter 21.0mm, Inside Diameter 14.6mm, Static Bend Radius 35mm, Reel Length 10 Meters, IP66, IP67 Rating, Galvanised Steel and Kraft Paper Core with PVC Covering, Black

### Ordering

EAN	5011949214439
Customs Tariff Number	8307106000

### Dimensions

Product Net Weight	6.9 lb 3.129 kg
--------------------	--------------------

### Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1 in 25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

---

### Additional Information

Application	Indoors / Outdoors, Marine, Buildings, Infrastructure
Brand / Label	Kopex
Color	Black
Inside Diameter	14.6 mm
Material	Galvanized Steel and Kraft Paper Core with PVC Covering
Nominal Size	1/2 in NC20
Number of Batteries	0
Outside Diameter	21.0 mm
Product Name	FLEXIBLE METAL CONDUIT
Product Type	Liquid Tight Pliable Conduit
Radius	35 mm
Standards	BSI Kitemark KM-90009, Low Voltage Directive
UPC	786210272078

---

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	PSBF0410
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	PSBF0410

---

### Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5543 >> Liquid Tight Conduit

---

### Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems



Product image  
not available