



PCB TERMINAL BLOCKS

10mm Pitch Commercial Standard Profile Screw Terminal Blocks

- 1-12 pole solid block
- Moulded in grey UL94-V0 flame retardant PC
- Wire protector terminals
- 0.5-4.0mm² (30-12AWG) solid cable
- 0.5-2.5mm² (30-12AWG) stranded cable
- Guided pin alignment
- Captive screws
- Anti solder wicking terminals
-  approved


CTB2500



SPECIFICATION

Rating	24A/250V UL=18A/300V, VDE&IMQ=24A/250V
Dielectric strength	≥3kV
Impulse withstand voltage	6kV
Working temperature	85°C
Moulding	UL94-V0 flame retardant PC
Pin/terminal	Tinned, nickel plated brass
Wire protector	Tin plated, phosphor bronze
Screw/torque	M3 steel zinc plated, 0.5Nm
Recommended PCB hole size	ø1.3mm

TYPE NO.	POLES	LENGTH
CTB2500/1	1	10mm
CTB2500/1/15	1	15mm
CTB2500/2	2	15mm
CTB2500/3	3	25mm
CTB2500/4	4	35mm
CTB2500/5	5	45mm



- 1 - CTB2500/1
2 - CTB2500/1/15
3 - CTB2500/2

PCB
TERMINAL
BLOCKS

INTER-
CONNECTION

FUSES &
FUSE-
HOLDERS

LEDs &
INDICATORS

MINIATURE
SWITCHES

LIMIT &
SAFETY
SWITCHES

CONTROL
PRODUCTS

INTERFACE
MODULES &
SUPPORTS

RELAY
BASES

DIN RAIL
ENCLOSURES

BATTERIES

SOLAR
PANELS

TRANS-
FORMERS