PCB TERMINAL BLOCKS

5.08mm Pitch Screwless Pluggable Terminal

- 2-24 pole solid block (female)
- 2-16 pole solid block (male)
- Pluggable female and male connectors
- Also compatible with conventional 5.08mm
 pluggable terminal blocks
- Screwless wire retained by cage spring
- Optional mounting clip, CSTB9C can be removed after fitting
- Polarised mouldings
- Moulded in green UL94-V0 flame retardant PA
- 0.2-2.5mm² (24-14AWG) solid & stranded cable
- c¶us, ⊕ approved
- GWT compliant version also

SPECIFICATION	
Rating	18A/320V UL=14A/300V, IMQ=18A/320V
Dielectric strength	≥2.5kV
Impulse withstand voltage	4kV
Working temperature	110°C
Moulding	UL94-V0 flame retardant PA
Clamp/spring	Nickel copper flash brass

2.7 2.54 5.08 8.3 18,1 2.54 5.08 CSTB9208

Female connector


TYPE NO.	POLES	LENGTH
CSTB9208/2	2	10.2mm
CSTB9208/3	3	15.2mm
CSTB9208/4	4	20.3mm
CSTB9208/5	5	25.4mm
CSTB9208/6	6	30.5mm
CSTB9208/7	7	35.6mm
CSTB9208/8	8	40.6mm
CSTB9208/9	9	45.7mm
CSTB9208/10	10	50.8mm
CSTB9208/11	11	55.9mm
CSTB9208/12	12	61mm
CSTB9208/13	13	66mm

TYPE NO.	POLES	LENGTH
CSTB9208/14	14	71.1mm
CSTB9208/15	15	76.2mm
CSTB9208/16	16	81.3mm
CSTB9208/17	17	86.4mm
CSTB9208/18	18	91.4mm
CSTB9208/19	19	96.5mm
CSTB9208/20	20	101.6mm
CSTB9208/21	21	106.7mm
CSTB9208/22	22	111.8mm
CSTB9208/23	23	116.8mm
CSTB9208/24	24	121.9mm

Male connector

TYPE NO.	POLES	LENGTH
CSTB9308/2	2	11.36mm
CSTB9308/3	3	16.44mm
CSTB9308/4	4	21.52mm
CSTB9308/5	5	26.6mm
CSTB9308/6	6	31.68mm
CSTB9308/7	7	36.76.mm
CSTB9308/8	8	41.84mm
CSTB9308/9	9	46.92mm
CSTB9308/10	10	52mm
CSTB9308/11	11	57.08mm
CSTB9308/12	12	62.16mm
CSTB9308/13	13	67.24mm

TYPE NO.	POLES	LENGTH
CSTB9308/14	14	72.32mm
CSTB9308/15	15	77.4mm
CSTB9308/16	16	82.48mm



Mounting Clip

TYPE NO.
CSTB9C





BLOCKS

INTER-CONNECTION

> FUSES & FUSE-HOLDERS

LEDs & INDICATORS

MINIATURE SWITCHES

LIMIT & SAFETY SWITCHES

CONTROL PRODUCTS

INTERFACE MODULES & SUPPORTS

> RELAY BASES

ENCLOSURES

BATTERIES

TRANS-FORMERS

