


**ART.: 810711364001**

DLSB100 LED OPAL COVER - 95 mm



Art.: 810711364001, DLSB100 LED, Opal-white pmma diffuser, 14W, 4000K, Driver dali, Direct, White, Recessed round LED downlight for indoors, consisting of: Multi-purpose die-cast aluminium housing combines all functions: heat-sinking, ceiling trim, ceiling brackets and gear tray connection, Light-tight housing, Suitable for ceiling tile thickness from 1-25 mm Recessed frosted diffuser for optimal light distribution and high homogeneity, White modular reflector, ABS injection-molded with light-tight connection of LED board, Excellent heat dissipation through die-cast aluminium heat sink with FAST (Flexible Air Stream) Technology, Colour rendering index Ra > 80, Colour tolerance according to MacAdam ≤ 3 SDCM Also dimmable via TouchDIM®, Complete with electric converter, Protection class IP20 (IP54 for light emission surface for installation in closed ceilings)

<b>Connected load</b>	14 W
<b>Luminous flux</b>	1090 lm
<b>Efficiency</b>	78 lm/W
<b>Colour temperature</b>	4000K
<b>Colour rendering (CRI)</b>	80
<b>IP class</b>	20
<b>Nominal voltage</b>	220 – 240 V
<b>Colour</b>	RAL 9016
<b>UGR</b>	25,7

