

Forked clamps

With round clamping face



Version:

- Heat-treated steel
- Painted
- With round clamping face



Art. no.	26130 080
Slot width	22 mm
Length	250 mm
Suitable cheese-head screw DIN 912	M20, M22
Clamping shoe height	40 mm
Clamping shoe width	60 mm
Diameter	30 mm
Length 2	65 mm
Length 3	45 mm
DIN	6315

EAN-Code

4020772070762