

Electronic micrometer

With interchangeable anvil

Mitutoyo

Application:

For measuring the wall thickness of pipes and cylinders, rivet head heights, etc.

Execution:

- carbide-tipped measuring faces
- ABS function
- HOLD (measured value storage)
- Origin (measurement presetting)
- IP65

Advantage:

- For measuring different characteristics
- IP65

Delivery:

Includes box, setting standard (from 25 mm), adjustment wrench, battery, anvil



Art. no.	32017 501
Brand	MITUTOYO
Manufacturer Part Number	317-35 1-30
Display	Digital
Min./max. length measuring range in inches	0-1 in
Digit increment	0.00005 in
Measuring surface diameter	6.3 mm
Measuring arrangement	Plan
IP protection class	IP 65
Data transmission type	DIGIMATIC
Spindle clamping	Yes
Digit height	7.5 mm
Functions	ABS function, Origin (Dimension preset), Hold-function (AE lock), Automatic switch-off
Min./max. measurement force	5-10 N
Number of rechargeable batteries/batteries	1 PCS
Battery designation	1,5 V SR44
DIN	863
Measuring spindle increments	0.5 mm
Calibration Group	D
Gross Weight	0.555 kg
Product Group	3MA

EAN

4946368688824