

## ACCU TEC cordless angle screwdriver ASW-PC, 18 V, up to 60 Nm

programmable, verifiable screwdriver in line with ISO 5393, VDI/VDE 2647



### Application:

For driving and removing screws in poorly accessible places. Ideal for complex fittings, which can be divided into up to seven sections.

### Execution:

- freely-programmable parameters: rotational speed, rotational direction, angle of rotation, torque, threshold, time
- process optimisation through up to five program steps which can be individually adjusted to the screwing application.
- programmable fuel gauge on machine
- both clockwise and anti-clockwise rotation can be parameterised
- maintenance module detects the screw operations and calibration data
- constant speed until shut off
- angle heads can be adjusted through 360°
- tongue tools can be used



### Delivery:

no battery, charger, angle head or torque adjusting wrench.

<b>Art. no.</b>	<b>71038 097</b>
<b>Brand</b>	FEIN
<b>Manufacturer Part Number</b>	71126360000
<b>Model</b>	ASW 18-45 PC
<b>Motor design</b>	Brushless motor
<b>Number of rechargeable batteries/batteries</b>	0
<b>Battery voltage</b>	18 V
<b>Battery included</b>	No
<b>Min. torque</b>	20 Nm
<b>Min./max. torque</b>	20-45 Nm
<b>Max. torque</b>	45 Nm
<b>Min. idle speed</b>	25 rpm
<b>Max. idle speed</b>	310 rpm
<b>Gross Weight</b>	1.589 kg
<b>Product Group</b>	704

### EAN

4014586883847