



BE-8330 - BE-8455

**ERGO™ Slotted Straight Tipped
Screwdrivers with Stubby Rubber
Grip 0.6-1.2 mm**



PRODUCT DETAILS









- Screwdriver developed according to the scientific ERGO™ process
- For slotted head screws, stubby-type for working in confined spaces
- Phosphate finished tip for higher accuracy
- three-component handle for maximum user comfort, soft material with ridged surface provides superior grip and greater force transmission
- Maximum comfort with minimum effort thanks to an ergonomic design
- Easy to choose the right tip with the colour-coded handle and permanent symbol on the domed end
- Flat face to prevent rolling away
- Integrated hanging hole
- High-performance alloy steel blade with chrome plating, entirely hardened for high protection against corrosion, long life tool
- Standards: ISO 2380 and DIN 5264



Follow the Fish!



PRODUCT ATTRIBUTES

| Product |  |  |  |  |  |  |  |  |
|----------------|---|---|---|---|--|---|---|---|
| BE-8330 | 0.6 mm | 3.5 mm | 25 mm | 3.5 mm | 36 mm | 58 mm | 83 mm | 37 g |
| BE-8340 | 0.8 mm | 4.0 mm | 25 mm | 4 mm | 36 mm | 58 mm | 83 mm | 38 g |
| BE-8350 | 1.0 mm | 5.5 mm | 25 mm | 5.5 mm | 36 mm | 58 mm | 83 mm | 40 g |
| BE-8450 | 1.0 mm | 5.5 mm | 45 mm | 5.5 mm | 36 mm | 58 mm | 103 mm | 44 g |
| BE-8355 | 1.2 mm | 6.5 mm | 25 mm | 6.5 mm | 36 mm | 58 mm | 83 mm | 43 g |
| BE-8455 | 1.2 mm | 6.5 mm | 45 mm | 6.5 mm | 36 mm | 58 mm | 103 mm | 48 g |
| BE-8360 | 1.2 mm | 8.0 mm | 25 mm | 8 mm | 36 mm | 58 mm | 83 mm | 44 g |

