



CE



CEE 7/VII



light source
work equipment
connected load
power consumption
light distribution
direct ratio
colour temperature
colour temperatur
color rendering index (CRI)
system of protection
class of protection
technology
operation
housing
cover
arm
balance of articulation joints
weight (net)
mains lead
fastening
lens, dimensions
lens material
lens, diopters
special features

LED
electronic transformer
100-240 V, 50/60 Hz
env. 16 W
direct
approx. 100 %
neutral white
approx. 4.000 K
>= 90 (R9>50)
IP 20
I
multi-stage switchable; continuously dimmable
multi-function switch
plastic; ESD-version; black
screen, milky; Polyamide
tubular aluminium section; ESD-coat of lacquer;
black
spring
env. 2,7 kg
approx. 3,3 m; mains plug; CEE 7/VII
screw-down flange
Ø 160 mm
glass
3,5
Ra (luminaire) ca. 90; ESD version; long arms; light
characteristic can be adjusted with a three-way
switch