



## 2740

Headlamp

Compact, reliable headlight for harsh conditions - the 2740 LED Headlamp features 3 LEDs, two white and one red. The red LED is very useful for preserving your night vision and the dual white LEDs produce up to 66 lumens of brilliant white light. A low level mode provides extended run time of 21 hours. Designed with weather resistant casings which also allows for fast and easy battery change.

Switch to the new 2740 Headlamp from Peli.

- Built Peli tough
- Hands-free design
- Night vision friendly
- Comfortable Cloth Strap



### DIMENSIONS

**Length** 2.25" (5.7 cm)

### MATERIALS

**Body** Polycarbonate (PC)

**O-Ring** Over-molded TPR

**Lens** Polycarbonate (PC)

**Shroud** Polycarbonate (PC)

### COLOURS

■ Black

■ White

■ Translucent Blue

### LIGHT SPECS

**Lamp Type** LED

### POWER

**Battery Size** AAA

**Battery Type** Alkaline

**Battery Quantity** 3

**Batteries Included** yes

**Volts** 4.5v

### WEIGHT

**Weight With Batteries** 3.3 oz (94 gr)

**Weight Without Batteries** 2.0 oz (57 gr)

### SWITCH

**Switch Type** Push Button

**Light Modes** High / Low / Flashing

### OTHER


**Minimum Pack** 1

**Package Code** C

Peli

c/ Provença, 388, Planta 7 • Barcelona, Spain 08025 • Phone: +34 934 674 999

[info@peli.com](mailto:info@peli.com) [www.peli.com](http://www.peli.com)

<b>FL1 STANDARD</b>	<b>HIGH</b>	<b>LOW</b>
	66 LUMENS	36 LUMENS
	7h 15mins	21h 0mins
	22m	16m
	122cd	68cd
	IPX4	

ACCESSORIES