

## FEATURES

- Cable protection
- Slotted construction
- Significantly lower fire risk, due to self-extinguishing nature
- Slot gaps are 8mm

## RS PRO Grey Slotted Panel Trunking - Narrow Slot, W40 mm x D40mm, L1m, PVC

RS Stock No.: 879-3725



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Brought to you by RS Pro, this open slot PVC cable trunking is versatile and cost effective. Used in any application where cable protection is essential, this cable trunking has flexible slots to allow easy slide-on and slide-off of the cable cover. The open slot construction also allows for cables to be threaded into and out of the trunking at any point. The trunking is made from high impact, warp proof PVC, and is self-extinguishing to UL94-V2. This means the trunking is suitable for commercial applications, with an emphasis on safety and long-life. Whether you are running cable from switchboards for IT applications, or power and network leads for a busy office or factory floor, this cable trunking is ideal. All models are highly reliable and excellent quality.

## General Specifications

<b>Trunking/Chain Type</b>	Slotted Panel Trunking
<b>Material</b>	PVC
<b>Colour</b>	Grey
<b>Fire Behaviour</b>	Self-extinguishing
<b>Applications</b>	PVC Trunking offered is developed using advanced extrusion process that allows for smooth process flow as well as ensures in the end products international quality standard

## Mechanical Specifications


<b>Length</b>	1m
<b>Width</b>	40mm
<b>Depth</b>	40mm
<b>Slot Type</b>	Open
<b>Slot Gap</b>	8mm

## Operation Environment Specifications

Maximum Service Temperature	85°C
-----------------------------	------

## Approvals

Standards Met	CSA Certified, RoHS Compliant, UL 94 V-2, E97527
---------------	--



RS Article No	W(mm)	H(mm)	A	Slot	Length
879-3741	40	60	17.5	4mm	1M
879-3747	40	80	17.5		
879-3750	60	80	27.5		
879-3725	40	40	17.5	8mm	
879-3731	40	60	17.5		
879-3738	40	80	17.5		
879-3744	60	80	27.5		