

Order code	Manufacturer code	Description
35-0276	n/a	12V PCB ELECTRO MECH INDICATOR (RC)

	Page 1 of 2
The enclosed information is believed to be correct, Information may change without notice due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 20/02/2007

1

2

3

4

5

6

7

8

A

A

B

B

C

C

D

D

E




E

F

F

SPECIFICATION

- 1. Rated Voltage 12VDC
- 2. Operating Voltage 8~15VDC
- 3. Max. Rated Current 30mA/12VDC
- 4. Min. Sound Pressure Level 85dB/10cm
- 5. Resonant Frequency 2300±300Hz
- 6. Response Time 50ms
- 6. Case Material PBT
- 7. Operating Temperature -20~+85°C
- 8. Store Temperature -20~+88°C
- 9. Weight 2g



				Compliance with ROHS	
				Magnetic Buzzer EFK1212	
No.	DESCRIPTION	APPROVED	DATE		
TOLERANCES UNLESS NOTED OTHERWISE: X ± .XX ± .XXX ± 90° FORMED ±° ANGLES ±°		APPROVALS		UNIT	DWG NO.
		DRAWN		mm	EF5.56.201
		CHECKED		SCALE	SHEET
		APPROVED	06.07.10	NOT TO SCALE	VER 1.0

1

2

3

4

5

6

7

8