

20 Port USB Fast Charger



TIGER PART: TGR-20P-USB

Features:

- 20 ports x 2 amp fast charging outputs
- Can provide up to 2.4 amps per port depending on number of devices connected (max. load 200W)

Six Safety Protection System



The Tiger Power range of USB chargers are safety approved and highly reliable, meeting latest level VI energy efficiency legislation. The TGR-20P-USB model has 20 ports, allowing for an office or classroom to charge their device quickly, all at the same time via the 2 amp outputs (2.4A max. 200W total load) Suitable for a wide range of applications.

Part number (no mains cable included):	TGR-20P-USB-NC
Part number (Supplied with separate UK cable) :	TGR-20P-USB
Part number (European cable):	TGR-20P-USB-EU
Input voltage:	220-240vac (230vac nominal.)
Input frequency:	50Hz
Output voltage:	5vdc
Current:	2 amps max. x 20 ports
Power :	20 Ports x 2A (2.4A max.) Fast Charging (200W max)
Powered by:	Internal high quality power supply (supplied)
Dimensions:	180 x 146 x 64mm
Weight:	2050g
AC cord length (where supplied):	1.8 metres
DC cord length:	Not applicable
DC connector:	USB type A
Polarity:	Standard
Efficiency:	89%
Input current RMS Max.:	2.0A
Inrush Current at 230vac:	120A max. at 220vac cold start, max. load
Load regulation:	+ / - 5%
Safety approval:	62368-1
M.T.B.F:	50,000 hours (MIL-HDBK-217F) at 25 degrees C
Operating temperature:	0°C to + 40°C

TIGER POWER PRODUCTS – QUALITY & RELIABILITY


This specification is not for general release or circulation. Tiger Power reserves the right to make changes to spec. or product without notice or liability.

20 Port USB Fast Charger

TIGER PART: TGR-20P-USB



The supreme charging solution
Detects your devices and delivers the fastest possible charge



High Compatibility
Compatible with all USB smart devices



Integrated on/off switch and universal IEC input supplied complete with AC mains cable

TIGER POWER PRODUCTS – QUALITY & RELIABILITY

This specification is not for general release or circulation. Tiger Power reserves the right to make changes to spec. or product without notice or liability.