

MASI20 INSTALLATION TECHNOLOGY

Distributor AS-I and extern power, 3 potentials




5 ports, universal

3 potentials

5 plug terminals included

[Link to Product](#)

Illustration



Product may differ from image

Approvals

The information in this brochure has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 05/15

Murrelektronik GmbH | Falkenstraße 3, 71570 Oppenweiler | Fon +49 (71 91) 47-0, Fax +49 (71 91) 47-491000 | shop@murrelektronik.de | shop.murrelektronik.de



Technical Data

Operating voltage	max. 36 V DC
Current per connection	max. 8 A
Total current	max. 12 A
Isolation voltage	AS-Interface/Power 200 V, Power/Power 50 V (EN 60664-1)

General data

Protection	IP20
Connection	Screw terminal: single wire (0.2...2.5 mm ²), stranded wire (0.2...1.5 mm ²)
Mounting method	DIN-rail mountable (EN 60715)
Temperature range	-20...+70 °C
Dimensions H × W × D	25×61×152 mm

Commercial data

country of origin	CZ
customs tariff number	85366990
minimum order quantity	1