



SINAMICS LINE REACTOR 380-480V 3AC 47-63HZ I<sub>LN</sub> = 4,0A  
STANDALONE

Order number	6SL3203-0CE13-2AA0
Phase number / of the input voltage	3
Type of voltage / of the input voltage	AC
Input voltage	380 ... 480
Output current / Rated value	4 A
Active power loss	
• at 50 Hz	Wert fehlt!
• at 60 Hz	Wert fehlt!
Type of electrical connection	
• for mains supply line	screw-type terminal
• for load-side outgoing feeder	screw terminals
Type of connectable conductor cross-section / for load-side outgoing feeder	Wert fehlt!
Connectable conductor cross-section	
• for mains supply line	4 mm <sup>2</sup>
• for load-side outgoing feeder	4 mm <sup>2</sup>
Type of electrical connection / for PE conductor	M4 x 8, washer, spring lock washer
Protection class IP	IP20
Width	125 mm
Height	120 mm
Depth	71 mm
Net weight	1.1 kg
Certificate of suitability	cURus

### Further information

#### Information und Download Center

[https://www.automation.siemens.com/mcms/infocenter/content/en/Pages/order\\_form.aspx](https://www.automation.siemens.com/mcms/infocenter/content/en/Pages/order_form.aspx)

**Technical documentation**

<http://w3.siemens.com/mcms/mc-solutions/en/motion-control/support/technical-documentation/Pages/technical-documentation.aspx>

**Industry Mall**

<https://eb.automation.siemens.com/mall/en/WW/Catag/Product/6SL32030CE132AA0/all>

**Industry Online Support**

<http://support.automation.siemens.com/WW/view/en/6SL32030CE132AA0/all>