

MNX PC 150/50 LG



Sample photo

Order symbol: PC 150/50 LG
Product nbr: 6012314
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074022141
EI. number:
 Finland: 3420345
 Electric No. Denmark: 8212022137
 Electric No. Italy: 7351075
 Electric No. Sweden: 2535542

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Accessories:		
mm:		180	130	50	MIN 10	DIN-15 Mounting rail	
inch:		7.1	5.1	2.0	MIN 15	DIN-15 Mounting rail	
Materials:						MIV 10	DIN-35 Mounting rail
Material:	Polycarbonate					MIV 15	DIN-35 Mounting rail
Base colour:	RAL 7035 -light grey					FP A 150/180	Front plate (Aluminium)
Cover screws material:	Polyamide					HFP 180	Front plate hinge series
Cover colour:	RAL 7035 -light grey					FP 22046	Wall fastening lug (4 pcs)
Cover screws colour:	Grey					Rating:	
Gasket material:	TPE					Ingress Protection (EN 60529): IP66/IP67	
Temperatures:						Impact Resistance (EN 62262): IK08	
Temperature °C (short term):	-40 ... 120 °C					Electrical insulation: Totally insulated	
Temperature °C (continuous):	-40 ... 80 °C					Halogen free (DIN/VDE 0472, Part 815): 1	
Temperature °F (short term):	-40 ... 250 °F					UV resistance: UL 508	
Temperature °F (continuous):	-40 ... 175 °F					Flammability Rating: UL 746C 5"	
Accessories:						Glow Wire Test (IEC 695-2-1) °C: 960	
MIV 150	Mounting plate (Galvanized steel)					NEMA Class: NEMA 1, 4, 4X, 6	
						Certificates:	
						Germanischer Lloyd (GL)	
						SGS Fimko	
						Gost R	

