



- NOTE:
- Electrical test:
A:MINI DP connector text:
(1). Insulation resistance:DC 300V 10M ohm;
(2). Contactor resistance:3 ohm;
(3). Dielectric strength:150V AC/Sec, 1mA.
B:Finished testing text condition:
(1) 100% open short & miss wire test
(2) Displayport practical application Test Pass
 - PACKING: 1PCS/SYNERGY 21 PE BAG+LABEL
 - ROHS COMPLIANT
 - PRINT WORD: DisplayPort Cable E119932-1 兄 AWM
STYLE 20276 80°C 30V VW-1 Copartner




⑬	PE BAG	SYNERGY 21 SLIP PE BAG	1	
⑫	LABEL	NO DRY GLUE LABEL	1	
⑪	MINI TIE	WHITE	2	
⑩	THUMB SCREW	#40-40(B-L30. 5 WHITE PVC)NICKEL PLATED	2	
⑨	DUST CAP	HDB 15P MALE LDPE	1	
⑧	DUST CAP	MINI DP 20PIN MALE LDPE	1	
⑦	MOLDED	45P WHITE PVC	2	
⑥	INTER MOLD	LDPE	2	
⑤	TUBE	∅0. 8*10 HEAT SHRINK TUBE	2	
④	TUBE	∅2. 0*5 HEAT SHRINK TUBE	10	
③	CONNECTOR	HDB 15P/M SOLDER TYPE, BLUE INSULATION, THE PIN GOLD PLATED, THE SHELL FOR GOLD PLATED, PCB WITH IC(NXP-PIN33928S)	1	
②	CONNECTOR	MINI DP 20P/M SOLDER TYPE, BLACK INSULATION, THE PIN GOLD PLATED, THE SHELL FOR GOLD PLATED	1	
①	CABEL	32AWG(7/0. 08TC*1P+7/0. 08TC+FAM)*5PCS+7/0. 08TC*5C+AL-FIOL+7/0. 08TC+BRAID 16/5/0. 12 AL-MG WHITE PVC OD5. 5MM±0. 2	1	

NO.		PARTS NAME		SPECIFICATION DESCRIPTION		QTY	REMARK
SYNERGY 21							
CUSTOMER		PRODUCT NAME		ITEM NO.		S216367	
MINI DP/M to VGA/M		DRAWNBY		MANUFACTURE COUNTRY:		CHINA	
SYNERGY 21		CHECKBY		APPROBY		DATE	
SYNERGY 21		SYNERGY 21		SYNERGY 21		2012. 08. 14	

BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.	SYNERGY 21	SYNERGY 21	SYNERGY 21	DATE
			2012. 08. 14	A				2012. 08. 14

Chart:

COLOR: WHITE		
ITEM	LENGTH	PACKING
S216367	3000±50MM	SYNERGY 21 Bag B



SYNERGY 21

CUSTOMER		PRODUCT NAME		DRAWNBY		SYNERGY 21		DATE		REV.	
		MINI DP/M to VGA/M		CHECKBY		SYNERGY 21		2012. 08. 14		A	
ITEM NO.		MANUFACTURE COUNTRY:		APPROBY		DATE		UNIT		MM	
S216367		CHINA		SYNERGY 21		2012. 08. 14					
REVISION RECORD MODIFICATIONS											
BY		CHK		DATE		REV.		DATE		REV.	