

Nuts

For ‚Rhombus‘ T-grooves



Application:

For inserting sliding block from above through the neck of the T-groove.

Version:

- Tempered
- The reduced contact surface in the T-groove results in a lower load capacity compared with comparable DIN 508 sizes.



Art. no.	26194 010
Nominal dimension of groove	12 mm
Slot nut width	11.7 mm
Thread dimension	M10
Height	14 mm
Slot nut height	7 mm
Length	18 mm
Property class	8

EAN-Code

4020772080259