

Drawer cabinets

Mobile with a pair of roller carriers and nylon rollers Ø 100 mm



Application:

For day-to-day hard use in workshops

Version:

- All drawers with full extension
- Standard individual drawer lock to prevent tipping of the cabinet
- Perforated, slotted drawers provide a strong hold
- Very robust construction for stringent and wide-ranging requirements

Advantage:

- Optimum drawer surface height provides ideal protection against items falling out and becoming lost
- Folding handle strips for simple, clean and protected labelling
- High quality - made in Germany and Swiss-made
- Runs perfectly smoothly and easily due to crossbar-less differential extension
- Full extension - clear overview and optimal access

Delivery:

1 anti-roll-off edging, 4-sided, 1 sliding rod, 1 roller carrier pair with nylon rollers Ø 100 mm



| | |
|--|--|
| Art. no. | 50301 083 |
| Number of drawers | 6 PCS |
| Height | 890 mm |
| Width | 564 mm |
| Depth | 725 mm |
| Height x width x depth | 890 x 564 x 725 mm |
| Housing height | 700 mm |
| Draw width (inner dimension) x drawer depth (inner dimension) | 450 x 600 mm |
| Load-carrying capacity per drawer | 75 kg |
| Drawer lock | Single lock right |
| Drawer front height | 1 x 50 mm, 2 x 75 mm, 2 x 100 mm, 1 x 200 mm |
| Body colour | Light grey RAL 7035 |
| Colour of front | Light grey RAL 7035 |
| Cabinet equipment | Pair of castors |
| With sliding handle | Yes |
| Height of roller carrier pair | 137 mm |
| Wheel diameter | 100 mm |
| Material of wheel | Nylon (polyamide) |
| Information about the direction | Along |
| Load-carrying capacity of roller | 400 kg |
| Opening/closing system | Key Lock |
| Rim height | 53 mm |
| Clear height | 600 mm |
| LISTA unit | 27 x 36 E |

EAN-Code

7612269060294