

**PAC
PAC-UNIV-HE16-F-2M**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Similar to illustration

Cable preconfeccionado cable plano según IEC-603/
DIN41651.

- Cable plano - cable plano
- Cable plano - punteras

General ordering data

Type	PAC-UNIV-HE16-F-2M
Order No.	1349770020
Version	Pre-assembled cable, PAC
GTIN (EAN)	4032248330300
Qty.	1 pc(s).

PAC PAC-UNIV-HE16-F-2M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Net weight	142 g
------------	-------

Temperatures

Operating temperature, max.	50 °C	Operating temperature, min.	-10 °C
Storage temperature, max.	60 °C	Storage temperature, min.	-10 °C
Operating temperature	-10...50 °C	Storage temperature	-10...60 °C

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General Data

Connector PLC side	H0.14/10 (FERRULES 0.14mm ²)	Interface connector	HE10 16P
Number of poles, min.	16-pole	Outer diameter	8 ± 1 mm
Cable	Cable LiYY	Cable length	2 m
Material	PVC	Wire cross-section	0.14 mm ²

Electrical Data

Rated voltage (text)	≤ 60 V DC ≤ 25 V AC	Permissible current strength per path, max.	1 A
Total current, max.	3 A	Resistance	≤ 150mΩ/m

Classifications

ETIM 5.0	EC000237	ETIM 6.0	EC000237
eClass 6.2	27-24-92-05	eClass 7.1	27-24-92-05
eClass 8.1	27-24-92-05	eClass 9.0	27-24-22-20
eClass 9.1	27-24-22-20		

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	Colours chart
--------------------	-------------------------------