

Product information

00 21 34 HL S2

Tool Case “Robust23 Start” Electric 24 parts



- Equipped with 6 KNIPEX tools, a total of 24 brand tools
- For the toughest conditions: Dust-tight, waterproof and temperature-resistant
- Max. payload: 25 kg
- Volume: 23 litres
- Fit-to-fly case, made from impact-resistant polypropylene
- Tool panels made of dirt-repellent PP twin-wall sheets with tool pockets and straps
- Base tray with aluminium inserts
- Air pressure compensation valve
- Temperature-resistant from - 30°C to +80° C
- Padlock eyelets
- Dimensions exterior (W x H x D): 470 x 370 x 190 mm; dimensions interior (W x H x D): 437 x 307 x 172 mm

General

Article No.	00 21 34 HL S2
EAN	4003773087366
Weight	6,800 g
Dimensions	370 x 190 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Dimension exterior (interior) width mm	470 mm (437 mm)
Dimension exterior (interior) height mm	370 mm (307 mm)
Dimension exterior (interior) depth mm	190 mm (172 mm)

technical change and errors excepted



