


G4 & G9

- Exact Replacements for 15w and 18w Halogens
- 3000K Output

Reflector

- Replacements for 40w, 50w and 60w Incandescent
- 2700K Output

- Easy Replacement
- True retro fit
- IC Drivers
- Flicker Free Design
- Automated Production
- Instant light
- Even Light Distribution



G4 – 15W REPLACEMENT – 25,000 HOURS

Part Number	Pack	Watt.	Cap	Dimmable	Life	Lumen	Colour Temp.	Lamp Dims.	Inner Qty.	Outer Qty.
S8099	Blister	1.8w	G4	x	25000 hrs	130lm	3000K	8x35	12	72

G9 – 18W REPLACEMENT – 15,000 HOURS

Part Number	Pack	Watt.	Cap	Dimmable	Life	Lumen	Colour Temp.	Lamp Dims.	Inner Qty.	Outer Qty.
S8100	Blister	2w	G9	x	25000 hrs	180lm	3000K	14x48	12	72

R50 REFLECTOR – 40W REPLACEMENT – 25,000 HOURS

Part Number	Pack	Watt.	Cap	Dimmable	Life	Lumen	Colour Temp.	Lamp Dims.	Inner Qty.	Outer Qty.
S9014	Box	6w	E14	x	25000 hrs	430lm	2700K	50x83	12	72

R63 REFLECTOR – 50W REPLACEMENT – 25,000 HOURS

Part Number	Pack	Watt.	Cap	Dimmable	Life	Lumen	Colour Temp.	Lamp Dims.	Inner Qty.	Outer Qty.
S9015	Box	9.5w	E27	x	25000 hrs	600lm	2700K	63x106	12	72

R80 REFLECTOR – 60W REPLACEMENT – 25,000 HOURS

Part Number	Pack	Watt.	Cap	Dimmable	Life	Lumen	Colour Temp.	Lamp Dims.	Inner Qty.	Outer Qty.
S9016	Box	11w	E27	x	25000 hrs	800lm	2700K	80x114	12	48