

## META CLIP boltless rack with shelves

Load capacity per bay 100/230 kg, zinc plated



### Application:

Universal rack system for all storage applications, quick setup or conversion through simple plugging of the shelves, can be assembled without tools.

### Execution:

- Double-row boltless rack with pre-assembled frame = clinched frame
- Both rows securely connected on the back
- Shelves height-adjustable, spacing 25 mm
- Shelves with a 50 mm hole grid to accommodate accessories
- Basic rack planning dimensions: Nominal length + 56 mm, 2 x nominal depth + 75 mm

### Advantage:

- Quick plug-in assembly without tools
- Stable and reliable
- Different versions available



<b>Art. no.</b>	<b>50167419</b>
<b>Brand</b>	META
<b>Manufacturer Part Number</b>	20070596
<b>Height</b>	3000 mm
<b>Length</b>	1056 mm
<b>Depth</b>	436 mm
<b>Nominal length</b>	1000 mm
<b>Nominal depth</b>	400 mm
<b>Design</b>	Shelving unit
<b>Type of assembly</b>	To insert
<b>Surface</b>	Zinc plated
<b>ESD-capable</b>	No
<b>Design of the frame</b>	Pre-assembled
<b>Grid dimension</b>	25 mm
<b>Number of shelves</b>	7 PCS
<b>Load-carrying capacity per shelf</b>	100 kg
<b>Load-carrying capacity per field</b>	1920 kg
<b>Number of frame</b>	2 PCS
<b>Number of lines</b>	2 PCS
<b>Quality label</b>	RAL-RG 614/1
<b>Made in</b>	Germany
<b>Material</b>	Steel
<b>Gross Weight</b>	77.116 kg
<b>Product Group</b>	508

### EAN

4026212100846