

## Compact angle grinder 125 mm

With variable rotation speed



### Application:

Compact angle grinders with variable speed for effective grinding and cutting work.

### Execution:

- Robust motor for daily use. Long-lasting thanks to overload protection and long carbon brush service life.
- Comprehensive user protection through rebound monitoring, restart protection, soft start and anti-vibration handgrip.
- The gear head can be rotated by 90° for a wide range of applications.
- Fast, tool-free changing of abrasives: Quick-release nut included as standard.
- High overload capability thanks to direct motor cooling.
- Industrial cable H07, 4 m length.
- Flexible application options due to variable speed.
- Fast work progress thanks to powerful motor.



<b>Art. no.</b>	<b>70374 008</b>
<b>Brand</b>	FEIN
<b>Manufacturer Part Number</b>	72228260000
<b>Model</b>	CG 17-125 INOX
<b>Manufacturer Article Number</b>	72228260000
<b>Battery included</b>	No
<b>Number of rechargeable batteries/batteries</b>	0
<b>Washer diameter</b>	125 mm
<b>Power input</b>	1700 W
<b>Power output</b>	1010 W
<b>Idle speed</b>	7500 rpm
<b>Thread dimension of spindle</b>	M14
<b>Weight</b>	2.4 kg
<b>With restart protection</b>	Yes
<b>With soft start</b>	Yes
<b>With overload protection</b>	Yes
<b>With electronic feedback</b>	No
<b>With reverse switch off</b>	Yes
<b>With speed control</b>	Yes
<b>With disc brake</b>	No
<b>With quick clamping system</b>	No
<b>With dead man function</b>	No
<b>Sound-pressure level</b>	92 dB
<b>Noise level</b>	103 dB
<b>Gross Weight</b>	3576.000 g
<b>Product Group</b>	704

### EAN

4014586895024