

Safety coupling eSafe series 320 – DN 7.6, steel, zinc-plated

In line with ISO 4414 and EN 983



Application:

For connecting hoses to compressed air tools and compressed air machines.

Execution:

- High-performance coupling relieving pressure before uncoupling to eliminate the risk of hose backstroke
- Male threads on the coupling and nipple are factory-fitted with thread seals

Advantage:

- Pressure relief for improved safety
- Very high flow capacity
- Rugged and durable



Art. no.	75135 031
Brand	CEJN
Manufacturer Part Number	103202155
Type	with male thread
Connection thread	R 1/2 inch
Flow capacity	2250 l/min
Max. operating pressure	16 bar
Thread length	15 mm
Length	62.5 mm
Width across flats	20 mm
Min./max. temperature resistance	-20 to +100 °C
Gross Weight	0.097 kg
Product Group	7Al

EAN

7391390285645