

HNS S/E 9 W 2G7

PURITEC HNS | Germicidal ultraviolet lamps



Areas of application

- Efficient disinfecting of air, water and surfaces

Product benefits

- Effective and environment-friendly disinfection without chemicals
- Low mercury content
- Long lifetime due to specific coating
- Ozone-free

Product features

- Dominant wavelength: 254 nm (OFR version)







Product datasheet

Technical data

Electrical data

Nominal wattage	9.00 W
Nominal voltage	48.0 V
Nominal current	0.17 A
Lamp current	0.17 A

Photometrical data

Radiated power 200280 nm (UVC)	2.5 W

Dimensions & weight



Diameter	28.0 mm
Length	142.0 mm

Additional product data

Base (standard designation)	2G7
-----------------------------	-----

Capabilities

Burning position	s180

Country specific information

Product code	METEL code	SEG-No.	STK number	UK Org
4008321384911	OSRHNSSE9OFR	-	4933184	-

Product datasheet

Safety advice

PURITEC germicidal lamps emit high-intensity UV radiation that can cause sunburn and conjunctivitis. The skin and eyes must therefore not be exposed to direct or reflected unfiltered radiation.

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4008321384911	HNS S/E 9 W 2G7	Folding carton box 1	171 mm x 23 mm x 36 mm	0.14 dm ³	29.67 g
4008321384928	HNS S/E 9 W 2G7	Shipping carton box 10	183 mm x 101 mm x 113 mm	2.09 dm ³	378.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.