



TAMURA
ANZEN DENGU CO.,LTD

Anerkannt / Approved:

UL / C-UL
VDE
CCC
BEAB

Drahtanschluss lang: 2 x 68± 3 mm (Standard)

Verpackungsmöglichkeiten:

500 St. in Polybeutel


Leads long: 2 x 68± 3 mm (Standard)

Packing options:

500 pcs. in plastic bag


Bemessungswerte / Ratings

Art.-No.	Produkt – No.	Strom Current	Spannung Voltage	Bemessungstemperatur Functioning open temp. (C°)	Max. Grenztemperatur Max. overshoot temp. (C°)
750.065	V 06 F	3 A	250	65	200
750.076	V 0 F	2 A	250	76	200
750.086	V 1 F	2 A	250	86	95
750.098	V 2 F	3 A	250	102	200
750.115	V 3 F	3 A	250	115	200
750.127	V 4 F	3 A	250	127	200
750.133	V 13 F	3 A	250	133	200
750.136	V 5 F	3 A	250	136	200
750.139	V 6 F	3 A	250	139	200
750.145	V 7 F	3 A	250 </td <td>145</td> <td>200</td>	145	200



Dimensions [mm]	Value
A	8.9±1.0
B	2.5±0.1
C	3.0 and under
D	0.58±0.1
E	68±3.0

Functioning Temperature



Resistance value

