BB-485USBTB-2W-ABB-485USBTB2WLS-A

USB to RS-485 Miniature Converters



Features

- Connect RS-485 devices to your USB port
- RS-485 data rate up to 921.6 Kbps
- USB 2.0 (12 Mbps) compatible
- Convenient, quick inline installation
- Compact size fits into laptop bags; perfect for field service
- USB port-powered
- High retention USB port holds USB cables securely
- Removable terminal block for easy wiring
- Locked Serial number model versions
- USB cable included

Specifications

Serial Technology

■ **RS-485 2-Wire** Data A(-), Data B(+), Ground

Connector
Removable terminal block (28 to 16 AWG)

Data Rate
Up to 921.6 Kbps

USB Technology

Connector
USB Type B female, high retention port (1.54kg (15N))

pull force)

Standard 2.0 (backward compatible)

Data Rate
12 Mbps

Power

Source USB portInput Voltage 5 V_{DC}

Consumption ~ 0.5 W (low power device - draws less than 100 mA)

Software

Driver
FTDI Virtual COM Port (VCP) Driver

0/S Windows 98, ME, 2000, XP, Vista, 7 (32/64), 8 (32/64),

10

Mechanical

Dimensions
Enclosure
Weight
65.0 x 32.0 x 16.0 mm
In-line mounted, plastic
104.3 g with USB cable

Environmental

Operating Temperature 0 to +70 °C
Storage Temperature -40 to +85 °C

• Operating Humidity 0 to 95% (non-condensing)

Meantime Between Failures (MTBF)

MTBF 1869313 hours

MTBF Method MIL 217F Parts Count Reliability Prediction

Approvals, Directives, Standards

Approvals
FCC, CE

Directives 2014/30/EU – Electromagnetic Compatibility Directive 2011/65/EU amended by 2015/863/EU – Reduction of

Hazardous Substances Directive (RoHS)

2012/19/EU — Waste Electrical and Electronic Equipment (WEEE)

Multimedia Equipment – EmissionRequirements EN 55024 – Information Technology Equipment – Immunity Characteristics – Limits and Methods of

Measurement

EN 61000-6 — Generic Immunity Dtandard for Residential, Commercial and Light-industrial

Environments

Ordering Information

BB-485USBTB-2W-A USB to RS-485 2-Wire Converter

BB-485USBTB2WLS-A USB to RS-485 2-Wire Converter, Locked Serial

Number

Accessories – sold separately

• **BB-USBAMBM-3F** 0.9 m USB cable (one included)

BB-USBAMBM-6F 1.8 m USB cable

BB-TBKT6 5-position, 3.5mm, terminal block, pluggable, 8A,

300V

