

RoHS Compliant

MP002453 RJ45 Plastic C3 Panel Jack Dip 180° Screw






Specifications

IP Rating : IP67

Recommend Panel Thickness : 0.8mm to 4mm
Recommend Torque : 14 to 15Kgf-cm

Diagram



Dimensions : Millimetres

No.	Part Name	Material/Finish	Qty.
1	Housing	Thermoplastic; Colour: Black	
2	RJ45 Receptacle	Housing: Thermoplastic; Colour: Grey	1
		Contacts: Copper Alloy, Finish: Au Plated	'
3	Holder	Thermoplastic; Colour: Black	
4	EMI Shielded Plate	Copper Alloy; Finish: Ni Plated	2
5	Hex Nut	Thermoplastic; Colour: Black	4
6	Gasket	Silicone; Colour: Black	I
7	PCB	FR-4	2
8	Pin Header	Housing: Thermoplastic; Colour: Black	1
		Contacts: Copper Alloy, Finish: Au Plated	_ ' _
9	Glue	Epoxy; Colour: Black	-



MP002454 RJ45 Plastic C3 Shielded Panel Jack Screw Coupler




Specifications

IP Rating : IP67

Recommend Panel Thickness : 0.8mm to 4mm
Recommend Torque : 14 to 15Kgf-cm

Diagram



Dimensions : Millimetres

Recommend

Panel Cut-Out

No.	Part Name	Material/Finish	Qty.
1	Housing	Thermoplastic; Colour: Black	
2	RJ45 Receptacle	Housing: Thermoplastic; Colour: Grey	1
		Contacts: Copper Alloy, Finish: Au Plated	'
3	Holder	Thermoplastic; Colour: Black	
4	EMI Shielded Plate	Copper Alloy; Finish: Ni Plated	2
5	Hex Nut	Thermoplastic; Colour: Black	
6	Gasket	Silicone; Colour: Black	
	RJ45 Receptacle	Housing: Thermoplastic; Colour: Black	
7		Contacts: Copper Alloy, Finish: Au Plated	1
		Shell: Copper Alloy; Finish: Ni Plated	
8	Holder	Thermoplastic; Colour: Black	
9	PCB	FR-4	
10	Glue	Epoxy; Colour: Black	-



MP002455 RJ45 Plastic C3 Shielded Panel Mount Screw with Receptacle Coupler 90 Deg.




Specifications

IP Rating : IP67

Recommend Panel Thickness : 0.8mm to 4mm
Recommend Torque : 6 to 7Kgf-cm

Diagram



Dimensions: Millimetres

No.	Part Name	Material/Finish	Qty.
1	Housing	Thermoplastic; Colour: Black	
2	RJ45 Receptacle	Housing: Thermoplastic; Colour: Grey	1
		Contacts: Copper Alloy, Finish: Au Plated	
3	Holder	Thermoplastic; Colour: Black	
4	EMI Shielded Plate	Copper Alloy; Finish: Ni Plated	2
5	Hex Nut	Thermoplastic; Colour: Black	
6	Gasket	Silicone; Colour: Black	
7	PCB	FR-4	1
	RJ45 Receptacle	Housing: Thermal plastic; Colour: Black	'
8		Contacts: Copper Alloy, Finish: Au Plated	
		Shell: Copper Alloy; Finish: Ni Plated	
9	Glue	Epoxy; Colour: Black	-



MP002456 RJ45 Plastic C3 Shielded E1 Field Install able cable end Plug Screw





Specifications

IP Rating : IP67

Cable Diameter : 5mm to 6mm Recommend Gland Nut Torque : 9 to 10Kgf-cm

Diagram





Dimensions: Millimetres

No.	Part Name	Material/Finish	Qty.
		Housing: Thermoplastic; Colour: Clean	
1	RJ45 Plug	Contacts: Copper Alloy, Finish: Au Plated	
		Shell: Copper Alloy; Finish: Ni Plated	
2	Rubber Pad	Silicone; Colour: Black	
3	Screw Nut	Thermoplastic; Colour: Black	1
4	Housing	Thermoplastic; Colour: Black	
5	Gland	Silicone; Colour: Green	
6	Cage	Thermoplastic; Colour: White	
7	Gland Nut	Thermoplastic; Colour: Black	



MP002452 RJ45 Plastic C3 Shielded Panel Jack Screw with Cable + RJ Plug




Specifications

IP Rating : IP67

Recommend Panel Thickness : 0.8mm to 6mm
Recommend Torque : 19 to 20Kgf-cm

Diagram



Dimensions: Millimetres

No.	Part Name	Material/Finish	Qty.
1	Housing	Thermoplastic; Colour: Black	
2	RJ45 Receptacle	Housing: Thermoplastic; Colour: Grey	1
		Contacts: Copper Alloy; Finish: Au Plated	'
3	Holder	Thermoplastic; Colour: Black	
4	EMI Shielded Plate	Copper Alloy; Finish: Ni Plated	2
5	Hex Nut	Thermoplastic; Colour: Black	1
6	Gasket	Silicone; Colour: Black	1
7	PCB	FR-4	2
8	Pin Header	Housing: Thermoplastic; Colour: Black	1
8		Contacts: Copper Alloy; Finish: Au Plated	'
9	Glue	Epoxy; Colour: Black	-
10	Shrink Tube	L=20mm; Colour: Black	
11	Cable	CAT5E 24AWG×4P+AL/MY+D; Colour: Grey, OD=6mm	
		Shell: Cold Roll Steel, Finish: Ni Plated	1
12	RJ45 Plug	Contacts: Copper Alloy, Finish: Au Plated	
		Housing: Thermoplastic, Colour: Clean	





Part Number Table

Description	
RJ45 Shielded Ethernet Cable Assembly, RJ45 Plug to RJ45 Receptacle C3 Panel, Grey, 200mm, IP67	
RJ45 Shielded Receptacle Connector, 8P8C, C3 Panel Mount, IP67	
RJ45 Shielded Modular Coupler, Straight, C3 Panel Mount, IP67	
RJ45 Shielded Modular Coupler, Right Angle, C3 Panel Mount, IP67	
RJ45 Shielded Plug Connector, 8P8C, C3 Panel Mount, IP67	MP002456

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

