

Product information

78 13 125


Electronic Super Knips®

DIN ISO 9654



- With lead catcher - no uncontrolled loss of cut wire ends
- Cutting edge hardness approx. 54 HRC
- INOX tool steel
- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Ground, very sharp cutting edges without bevel
- Precisely shaped tips cut wires close to a surface from $\varnothing 0.2$ mm
- Shear cut with controlled micro cutting edge misalignment for the most precise cutting of even the thinnest of wires and for a long service life
- Joint with stainless steel rivet
- Extremely smooth movement for minimum operator fatigue
- With opening spring and opening limiter

General	
Article No.	78 13 125
EAN	4003773035398
Head	polished
Handles	with multi-component grips
Weight	57 g
Dimensions	125 x 48 x 12 mm
Standard	DIN ISO 9654
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Cutting capacities medium hard wire (diameter)	$\varnothing 1.0$ mm
Cutting capacities soft wire (diameter)	$\varnothing 0.2 - 1.6$ mm
Jaw length (B)	9 mm
Jaw thickness (joint) (D)	7.5 mm
Head width (A)	13.5 mm



technical change and errors excepted