

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936010637](#)  
**Status:** **Active**  
**Overview:** [GWconnect® Heavy Duty Connectors \(HDC\)](#)  
**Description:** [GWconnect® STD - Standard, Single Lever Hood, Polyamide, with 2 Pegs, Side Entry, Size 3A «21x21», Pg11 Thread, Grey White](#)

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Connectors / Enclosures
Series	<a href="#">93601</a>
Comments	IP67 with screw gasket.
Component Size	3A «21x21»
Component Type	Single Lever Hood
IP Rating	IP66
Overview	<a href="#">GWconnect® Heavy Duty Connectors (HDC)</a>
Product Category	Heavy Duty Connectors
Product Name	GWconnect®
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191839448
Use With	Size 3A «21x21» S-A, S-D, and S-Q Inserts

**Physical**

Entry Location	Side
Flammability	UL 94V-0
Hood Color	Grey White RAL 9002
Lock to Mating Part	Yes
Material - Hood	Polyamide
Material - Peg	Polyamide
Number of Pegs	2
Packaging Type	Bag
Thread Size	Pg11
Thread Type	(Pg)

**Electrical**

Voltage - Maximum	230V / 400V
-------------------	-------------

**Material Info**

Old Part Number	7803.6209.0
-----------------	-------------

GWconnect® is a registered trademark of Molex Incorporated in Italy and may be registered in other jurisdictions.



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

**Search Parts in this Series**

[93601](#) Series