

## Han M23 P Hood angl. 11-17mm rotatable



Part number	09 15 600 0604
Specification	Han M23 P Hood angl. 11-17mm rotatable
HARTING eCatalogue	<a href="https://b2b.harting.com/09156000604">https://b2b.harting.com/09156000604</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> M23 Power
Type of hood/housing	Hoods
Description of hood/housing	EMC version Rotatable

### Version

Locking type	Screw locking
Size	M23
Version	Angled entry

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP67 / IP69 / IPX9K acc. to ISO 20653 in locked position
Clamping range	11 ... 17 mm

### Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated

### Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
----------	--

### Commercial data

Packaging size	5
Net weight	166.75 g
Country of origin	Germany



**Pushing Performance**

## Commercial data

Customs tariff number	85366990
-----------------------	----------

---