

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1202540030](#)
Status: **Active**
Overview: Contrinex Inductive and Photoelectric
Description: Contrinex Photoelectric Sensor, C23 (20 x 30mm) Housing, Through-Beam (Receiver), 0 - 30000mm Operating Distance, PNP, Changeover/IOL, 4-pin M8 Connector

Documents:

[Product Specification 1202540030-000 \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Sensors
Series	120254
Exclude SD Check	Yes
IP Rating	IP67
Operating Principle	Through-Beam (Receiver)
Overview	<u>Contrinex Inductive and Photoelectric</u>
Product Category	Sensors
Product Literature Order No	987651-9403
Product Name	Contrinex
Type	Photoelectric
UPC	191130066766

Physical

Connection	Connector (M8, 4-pin)
Housing Size	20 x 30mm
Material - Housing	ABS
Material - Window	PMMA
Operating Distance	0 - 30000mm
Output	Changeover/IOL
Sensor Housing Size	C23
Temperature Range - Operating	-25° to +65°C

Electrical

Polarity	PNP
Switching Frequency	≤ 1000 Hz

Material Info

Engineering Number	LLR-C23PA-NMS-603
--------------------	-------------------

Reference - Drawing Numbers

Product Specification	1202540030-000
-----------------------	----------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[120254 Series](#)