

HellermannTyton

DATA SHEET


Connector Strips (NTPE)

Features

Easy cut & low-cost

All screws are captive & raised for easy wiring

Properties	
Inserts	Brass
Housing	Polyethylene
Temperature	80°C
Screws	Galvanised Steel
Standard	CE
Colour	Natural or Black



HT Code	Cross Section	Rated Current	Rated Voltage	Dimensions							
				L	W	Ø ₁	Ø ₂	D	d	H	h
CS3NTPE	4mm ²	3-24A	380V	93	16.8	2.8	2.3	7.8	6	13.6	7.6
CS5NTPE	6mm ²	5-32A	380V	115	18.8	3.3	2.6	10	8	15	8.8
CS10NTPE	10mm ²	10-57A	400V	129	20.7	4.3	2.8	11	9	16.2	9.6
CS15NTPE	12mm ²	15-61A	400V	137	22.5	4.5	2.8	12	10	18.8	10.2
CS30NTPE	16mm ²	30-76A	400V	165	25.5	5.5	3.0	14	11	19.8	11.2
CS60NTPE	25mm ²	60-101A	400V	187	31.2	6.5	3.8	16.5	13	25.5	14.8