

### Standard Thermocouple Socket with Stainless Steel mounting bracket

Types K, J, T  
(ANSI Colour Code)



- Standard size in-line Thermocouple Socket with stainless steel panel mounting bracket
- Intended for use in more industrial processes but can be used in all applications as desired
- Available in Thermocouple types K, J, T
- For Types K, J, T contacts are made from true Thermocouple alloys
- Colour coded in accordance with ANSI specification
- Maximum continuous operating temperature 220 deg°C

T/C Type	Colour Code (ANSI)	+Positive Contact (alloy type)	-Negative Contact (alloy type)	Manufacturer's Part Number	Rapid Order Code
K	Yellow	+Nickel Chromium	-Nickel Alloy	XE-1438-001	61-3085
J	Black	+Iron	-Copper Nickel	XE-9138-001	61-3086
T	Blue	+Copper	-Copper Nickel	XE-1528-001	61-3087

#### Schematic Drawing

