



SLIM LINE POTENTIAL TERMINAL BLOCK

Potential terminal block
SlimLine

[Link to Product](#)

Illustration



Product may differ from Image

Approvals



Technical Data

Operating voltage	max. 30 V AC/DC
Total current	max. 20 A
Input terminals	Spring clamp terminals: 0.08...2.5 mm ² (AWG 28...12)

General data

Protection	IP20
------------	------

The information in this brochure has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 05/15

Murrelektronik GmbH | Falkenstraße 3, 71570 Oppenweiler | Fon +49 (71 91) 47-0, Fax +49 (71 91) 47-491000 | shop@murrelektronik.de | shop.murrelektronik.de

Dimensions H x W x D	70x56x32.5 mm
Connection	Push-In 0.13...1.5 mm ² (AWG 28...16)
Temperature range	0...+55 °C (storage temperature -40...+85 °C)
Commercial data	
country of origin	DE
customs tariff number	85369010
minimum order quantity	1